

Frictional torque (Nm) for bore diameter (mm)

Size	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22
5	0,6	0,6	0,7	0,8																	
7			1.3	1.4	1.5	1.6															
9			2.3	2.4	2.5	2.7	2.8	2.9	3.0	3.2											
12			6.3	6.6	6.9	7.2	7.4	7.7	8.0	8.3	8.6										
14			7.7	8.0	8.3	8.6	8.9	9.2	9.4	9.7	10	10.3	10.6	10.9	11.2						
19									44	45	47	48	49	50	51	52	54	55	56	57	58

Frictional torque (Nm) for bore diameter (mm)

Size	15	16	19	20	22	24	25	28	30	32	35	38	39	40	42	44	45	46	48	50	52	54
24	64	65	69	70	72	74	76	79	81	84												
28			114	116	119	123	124	130	133	137	142											
38				135	138	142	144	149	152	156	161	166	168	169	173	176	178					
42							294	304	310	317	327	337	340	343	350	357	360	363	370	376		
48							476	491	500	510	524	539	544	548	558	568	572	577	587	596	606	616