

Pull handles, aluminium, round

Item description/product images

19"



Description

Material:
Aluminium.

Version:
Natural or black anodised.

Note for ordering:
Order the fastening material and end washers separately.

Assembly:
From the rear.


Accessory:
End washers K0201.

Pull handles, aluminium, round

Item description/product images



Drawings



Overview of items

Pull handles, aluminium, round

Order No.	Main colour	A	B	D	H	L	T	Load capacity N	Order No. end washer
K0201.032041	black	32	8	M4	32	40	10	500	K0201.4
K0201.055041	black	55	8	M4	32	63	10	500	K0201.4
K0201.064041	black	64	8	M4	32	72	10	500	K0201.4
K0201.076041	black	76	8	M4	32	84	10	500	K0201.4
K0201.088041	black	88	8	M4	32	96	10	500	K0201.4
K0201.096041	black	96	8	M4	32	104	10	500	K0201.4
K0201.098041	black	98	8	M4	32	106	10	500	K0201.4
K0201.100041	black	100	8	M4	32	108	10	500	K0201.4
K0201.102041	black	102	8	M4	32	110	10	500	K0201.4
K0201.120041	black	120	8	M4	32	128	10	500	K0201.4
K0201.136041	black	136	8	M4	32	144	10	500	K0201.4
K0201.055051	black	55	10	M5	40	65	10	500	K0201.1
K0201.064051	black	64	10	M5	40	74	10	500	K0201.1
K0201.076051	black	76	10	M5	40	86	10	500	K0201.1
K0201.088051	black	88	10	M5	40	98	10	500	K0201.1
K0201.096051	black	96	10	M5	40	106	10	500	K0201.1
K0201.098051	black	98	10	M5	40	108	10	500	K0201.1
K0201.100051	black	100	10	M5	40	110	10	500	K0201.1
K0201.102051	black	102	10	M5	40	112	10	500	K0201.1
K0201.120051	black	120	10	M5	40	130	10	500	K0201.1
K0201.136051	black	136	10	M5	40	146	10	500	K0201.1
K0201.140051	black	140	10	M5	40	150	10	500	K0201.1
K0201.160051	black	160	10	M5	40	170	10	500	K0201.1

Pull handles, aluminium, round

Overview of items

Order No.	Main colour	A	B	D	H	L	T	Load capacity N	Order No. end washer
K0201.180051	black	180	10	M5	40	190	10	500	K0201.1
K0201.200051	black	200	10	M5	40	210	10	500	K0201.1
K0201.235051	black	235	10	M5	40	245	10	500	K0201.1
K0201.250051	black	250	10	M5	40	260	10	500	K0201.1
K0201.300051	black	300	10	M5	40	310	10	500	K0201.1
K0201.350051	black	350	10	M5	40	360	10	500	K0201.1
K0201.120061	black	120	12	M6	42	132	12	500	K0201.6
K0201.136061	black	136	12	M6	42	148	12	500	K0201.6
K0201.140061	black	140	12	M6	42	152	12	500	K0201.6
K0201.160061	black	160	12	M6	42	172	12	500	K0201.6
K0201.180061	black	180	12	M6	42	192	12	500	K0201.6
K0201.200061	black	200	12	M6	42	212	12	500	K0201.6
K0201.235061	black	235	12	M6	42	247	12	500	K0201.6
K0201.250061	black	250	12	M6	42	262	12	500	K0201.6
K0201.300061	black	300	12	M6	42	312	12	500	K0201.6
K0201.350061	black	350	12	M6	42	362	12	500	K0201.6
K0201.140081	black	140	16	M8	58	156	12	500	-
K0201.160081	black	160	16	M8	58	176	12	500	-
K0201.180081	black	180	16	M8	58	196	12	500	-
K0201.200081	black	200	16	M8	58	216	12	500	-
K0201.235081	black	235	16	M8	58	251	12	500	-
K0201.250081	black	250	16	M8	58	266	12	500	-
K0201.300081	black	300	16	M8	58	316	12	500	-
K0201.350081	black	350	16	M8	58	366	12	500	-
K0201.200101	black	200	20	M10	70	220	19	500	-
K0201.235101	black	235	20	M10	70	255	19	500	-
K0201.250101	black	250	20	M10	70	270	19	500	-
K0201.300101	black	300	20	M10	70	320	19	500	-
K0201.350101	black	350	20	M10	70	370	19	500	-
K0201.032043	natural	32	8	M4	32	40	10	500	K0201.5
K0201.055043	natural	55	8	M4	32	63	10	500	K0201.5
K0201.064043	natural	64	8	M4	32	72	10	500	K0201.5
K0201.076043	natural	76	8	M4	32	84	10	500	K0201.5
K0201.088043	natural	88	8	M4	32	96	10	500	K0201.5
K0201.096043	natural	96	8	M4	32	104	10	500	K0201.5
K0201.098043	natural	98	8	M4	32	106	10	500	K0201.5
K0201.100043	natural	100	8	M4	32	108	10	500	K0201.5
K0201.102043	natural	102	8	M4	32	110	10	500	K0201.5
K0201.120043	natural	120	8	M4	32	128	10	500	K0201.5
K0201.136043	natural	136	8	M4	32	144	10	500	K0201.5
K0201.055053	natural	55	10	M5	40	65	10	500	K0201.3
K0201.064053	natural	64	10	M5	40	74	10	500	K0201.3
K0201.076053	natural	76	10	M5	40	86	10	500	K0201.3
K0201.088053	natural	88	10	M5	40	98	10	500	K0201.3
K0201.096053	natural	96	10	M5	40	106	10	500	K0201.3
K0201.098053	natural	98	10	M5	40	108	10	500	K0201.3
K0201.100053	natural	100	10	M5	40	110	10	500	K0201.3
K0201.102053	natural	102	10	M5	40	112	10	500	K0201.3
K0201.120053	natural	120	10	M5	40	130	10	500	K0201.3
K0201.136053	natural	136	10	M5	40	146	10	500	K0201.3
K0201.140053	natural	140	10	M5	40	150	10	500	K0201.3
K0201.160053	natural	160	10	M5	40	170	10	500	K0201.3
K0201.180053	natural	180	10	M5	40	190	10	500	K0201.3
K0201.200053	natural	200	10	M5	40	210	10	500	K0201.3
K0201.235053	natural	235	10	M5	40	245	10	500	K0201.3
K0201.250053	natural	250	10	M5	40	260	10	500	K0201.3
K0201.300053	natural	300	10	M5	40	310	10	500	K0201.3
K0201.350053	natural	350	10	M5	40	360	10	500	K0201.3
K0201.120063	natural	120	12	M6	42	132	12	500	K0201.7
K0201.136063	natural	136	12	M6	42	148	12	500	K0201.7
K0201.140063	natural	140	12	M6	42	152	12	500	K0201.7

Pull handles, aluminium, round

Overview of items

Order No.	Main colour	A	B	D	H	L	T	Load capacity N	Order No. end washer
K0201.160063	natural	160	12	M6	42	172	12	500	K0201.7
K0201.180063	natural	180	12	M6	42	192	12	500	K0201.7
K0201.200063	natural	200	12	M6	42	212	12	500	K0201.7
K0201.235063	natural	235	12	M6	42	247	12	500	K0201.7
K0201.250063	natural	250	12	M6	42	262	12	500	K0201.7
K0201.300063	natural	300	12	M6	42	312	12	500	K0201.7
K0201.350063	natural	350	12	M6	42	362	12	500	K0201.7
K0201.140083	natural	140	16	M8	58	156	12	500	-
K0201.160083	natural	160	16	M8	58	176	12	500	-
K0201.180083	natural	180	16	M8	58	196	12	500	-
K0201.200083	natural	200	16	M8	58	216	12	500	-
K0201.235083	natural	235	16	M8	58	251	12	500	-
K0201.250083	natural	250	16	M8	58	266	12	500	-
K0201.300083	natural	300	16	M8	58	316	12	500	-
K0201.350083	natural	350	16	M8	58	366	12	500	-
K0201.200103	natural	200	20	M10	70	220	19	500	-
K0201.235103	natural	235	20	M10	70	255	19	500	-
K0201.250103	natural	250	20	M10	70	270	19	500	-
K0201.300103	natural	300	20	M10	70	320	19	500	-
K0201.350103	natural	350	20	M10	70	370	19	500	-