

Frictional torque (Nm) for bore diameter (mm)																							
Size	4	6	8	10	14	15	16	18	20	22	24	25	28	30	32	35	38	40	42	45	48	50	55
14	11	16	21	26	37	39	42																
19			47	59	83	89	95	107	119														
24				59	83	89	95	107	119	130	142	148	166	178	190								
28					123	132	141	159	176	194	211	220	247	264	282	308							
38								159	176	194	211	220	247	264	282	308	335	352	370	396	423		
42										370	404	420	471	505	538	589	639	673	706	757	807	841	
48										539	588	612	686	735	784	857	931	980	1029	1102	1176	1225	1347