

Pull handles, steel round

Item description/product images

19"



Description

Material:
Steel.


Version:
high-gloss chromed.

Note for ordering:
Order the fastening material and end washers separately.

Application:
From the rear.

Accessory:
End washers K1823.
Washers K0868.
Washers K1150.
Hex head bolts K0871.
Screws K1796.
Cap screws K0869.

Drawings



Overview of items

Pull handles steel, round

Pull handles, steel round

Overview of items

| Order No. | A | B | D | H | L | T | Load capacity N |
|--------------|-----|----|-----|----|-----|----|--------------------|
| K1799.032031 | 32 | 5 | M3 | 24 | 37 | 6 | 500 |
| K1799.042031 | 42 | 5 | M3 | 24 | 47 | 6 | 500 |
| K1799.055031 | 55 | 5 | M3 | 24 | 60 | 6 | 500 |
| K1799.064031 | 64 | 5 | M3 | 24 | 69 | 6 | 500 |
| K1799.076031 | 76 | 5 | M3 | 24 | 81 | 6 | 500 |
| K1799.088031 | 88 | 5 | M3 | 24 | 93 | 6 | 500 |
| K1799.032041 | 32 | 8 | M4 | 32 | 40 | 8 | 500 |
| K1799.042041 | 42 | 8 | M4 | 32 | 50 | 8 | 500 |
| K1799.055041 | 55 | 8 | M4 | 32 | 63 | 8 | 500 |
| K1799.064041 | 64 | 8 | M4 | 32 | 72 | 8 | 500 |
| K1799.076041 | 76 | 8 | M4 | 32 | 84 | 8 | 500 |
| K1799.088041 | 88 | 8 | M4 | 32 | 96 | 8 | 500 |
| K1799.096041 | 96 | 8 | M4 | 32 | 104 | 8 | 500 |
| K1799.098041 | 98 | 8 | M4 | 32 | 108 | 8 | 500 |
| K1799.100041 | 100 | 8 | M4 | 32 | 108 | 8 | 500 |
| K1799.102041 | 102 | 8 | M4 | 32 | 110 | 8 | 500 |
| K1799.120041 | 120 | 8 | M4 | 32 | 128 | 8 | 500 |
| K1799.136041 | 136 | 8 | M4 | 32 | 148 | 8 | 500 |
| K1799.055051 | 55 | 10 | M5 | 40 | 65 | 10 | 1000 |
| K1799.064051 | 64 | 10 | M5 | 40 | 74 | 10 | 1000 |
| K1799.076051 | 76 | 10 | M5 | 40 | 86 | 10 | 1000 |
| K1799.088051 | 88 | 10 | M5 | 40 | 98 | 10 | 1000 |
| K1799.096051 | 96 | 10 | M5 | 40 | 106 | 10 | 1000 |
| K1799.098051 | 98 | 10 | M5 | 40 | 108 | 10 | 1000 |
| K1799.100051 | 100 | 10 | M5 | 40 | 110 | 10 | 1000 |
| K1799.102051 | 102 | 10 | M5 | 40 | 112 | 10 | 1000 |
| K1799.120051 | 120 | 10 | M5 | 40 | 130 | 10 | 1000 |
| K1799.136051 | 136 | 10 | M5 | 40 | 146 | 10 | 1000 |
| K1799.160051 | 160 | 10 | M5 | 40 | 170 | 10 | 1000 |
| K1799.180051 | 180 | 10 | M5 | 40 | 190 | 10 | 1000 |
| K1799.200051 | 200 | 10 | M5 | 40 | 210 | 10 | 1000 |
| K1799.235051 | 235 | 10 | M5 | 40 | 245 | 10 | 1000 |
| K1799.250051 | 250 | 10 | M5 | 40 | 260 | 10 | 1000 |
| K1799.300051 | 300 | 10 | M5 | 40 | 310 | 10 | 1000 |
| K1799.350051 | 350 | 10 | M5 | 40 | 360 | 10 | 1000 |
| K1799.120061 | 120 | 12 | M6 | 42 | 132 | 12 | 1000 |
| K1799.135061 | 136 | 12 | M6 | 42 | 148 | 12 | 1000 |
| K1799.160061 | 160 | 12 | M6 | 42 | 172 | 12 | 1000 |
| K1799.180061 | 180 | 12 | M6 | 42 | 192 | 12 | 1000 |
| K1799.200061 | 200 | 12 | M6 | 42 | 212 | 12 | 1000 |
| K1799.235061 | 235 | 12 | M6 | 42 | 247 | 12 | 1000 |
| K1799.250061 | 250 | 12 | M6 | 42 | 262 | 12 | 1000 |
| K1799.300061 | 300 | 12 | M6 | 42 | 312 | 12 | 1000 |
| K1799.350061 | 350 | 12 | M6 | 42 | 362 | 12 | 1000 |
| K1799.160081 | 160 | 16 | M8 | 58 | 176 | 12 | 1000 |
| K1799.180081 | 180 | 16 | M8 | 58 | 196 | 12 | 1000 |
| K1799.200081 | 200 | 16 | M8 | 58 | 216 | 12 | 1000 |
| K1799.235081 | 235 | 16 | M8 | 58 | 251 | 12 | 1000 |
| K1799.250081 | 250 | 16 | M8 | 58 | 266 | 12 | 1000 |
| K1799.300081 | 300 | 16 | M8 | 58 | 316 | 12 | 1000 |
| K1799.350081 | 350 | 16 | M8 | 58 | 366 | 12 | 1000 |
| K1799.200101 | 200 | 20 | M10 | 70 | 220 | 19 | 1000 |
| K1799.235101 | 235 | 20 | M10 | 70 | 255 | 19 | 1000 |
| K1799.250101 | 250 | 20 | M10 | 70 | 270 | 19 | 1000 |
| K1799.300101 | 300 | 20 | M10 | 70 | 320 | 19 | 1000 |
| K1799.350101 | 350 | 20 | M10 | 70 | 370 | 19 | 1000 |

