


Spherical knobs revolving

Item description/product images




Description

Version:

Trivalent blue passivated steel or bright stainless steel.

Circlips electro zinc-plated, including stainless steel version.

Drawings



Overview of items

Spherical knobs revolving

Order No.	Component material	Colour Cap	D	D1	D2	D3	D4	H	H1	H2	L	L2	L3	L4	SW
K0254.106	steel	black grey RAL 7021	M6	25	12	17	8	25	3	2	10	15	5	5	7
K0254.1061	steel	orange RAL 2004	M6	25	12	17	8	25	3	2	10	15	5	5	7
K0254.1062	steel	signal green RAL6032	M6	25	12	17	8	25	3	2	10	15	5	5	7
K0254.1063	steel	blue RAL5017	M6	25	12	17	8	25	3	2	10	15	5	5	7
K0254.1065	steel	light grey RAL 7035	M6	25	12	17	8	25	3	2	10	15	5	5	7
K0254.1066	steel	traffic red RAL 3020	M6	25	12	17	8	25	3	2	10	15	5	5	7
K0254.1067	steel	colza yellow RAL 1021	M6	25	12	17	8	25	3	2	10	15	5	5	7
K0254.208	steel	black grey RAL 7021	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
K0254.2081	steel	orange RAL 2004	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
K0254.2082	steel	signal green RAL6032	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
K0254.2083	steel	blue RAL5017	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
K0254.2085	steel	light grey RAL 7035	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8

Spherical knobs revolving

Overview of items

Order No.	Component material	Colour Cap	D	D1	D2	D3	D4	H	H1	H2	L	L2	L3	L4	SW
K0254.2086	steel	traffic red RAL 3020	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
K0254.2087	steel	colza yellow RAL 1021	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
K0254.310	steel	black grey RAL 7021	M10	40	19	23	13	41	4	3	15	25	7	10	10
K0254.3101	steel	orange RAL 2004	M10	40	19	23	13	41	4	3	15	25	7	10	10
K0254.3102	steel	signal green RAL6032	M10	40	19	23	13	41	4	3	15	25	7	10	10
K0254.3103	steel	blue RAL5017	M10	40	19	23	13	41	4	3	15	25	7	10	10
K0254.3105	steel	light grey RAL 7035	M10	40	19	23	13	41	4	3	15	25	7	10	10
K0254.3106	steel	traffic red RAL 3020	M10	40	19	23	13	41	4	3	15	25	7	10	10
K0254.3107	steel	colza yellow RAL 1021	M10	40	19	23	13	41	4	3	15	25	7	10	10
K0254.412	steel	black grey RAL 7021	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
K0254.4121	steel	orange RAL 2004	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
K0254.4122	steel	signal green RAL6032	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
K0254.4123	steel	blue RAL5017	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
K0254.4125	steel	light grey RAL 7035	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
K0254.4126	steel	traffic red RAL 3020	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
K0254.4127	steel	colza yellow RAL 1021	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
K0254.0106	stainless steel	black grey RAL 7021	M6	25	12	17	8	25	3	2	10	15	5	5	7
K0254.01061	stainless steel	orange RAL 2004	M6	25	12	17	8	25	3	2	10	15	5	5	7
K0254.01062	stainless steel	signal green RAL6032	M6	25	12	17	8	25	3	2	10	15	5	5	7
K0254.01063	stainless steel	blue RAL5017	M6	25	12	17	8	25	3	2	10	15	5	5	7
K0254.01065	stainless steel	light grey RAL 7035	M6	25	12	17	8	25	3	2	10	15	5	5	7
K0254.01066	stainless steel	traffic red RAL 3020	M6	25	12	17	8	25	3	2	10	15	5	5	7
K0254.01067	stainless steel	colza yellow RAL 1021	M6	25	12	17	8	25	3	2	10	15	5	5	7
K0254.0208	stainless steel	black grey RAL 7021	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
K0254.02081	stainless steel	orange RAL 2004	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
K0254.02082	stainless steel	signal green RAL6032	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
K0254.02083	stainless steel	blue RAL5017	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
K0254.02085	stainless steel	light grey RAL 7035	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
K0254.02086	stainless steel	traffic red RAL 3020	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
K0254.02087	stainless steel	colza yellow RAL 1021	M8	32	15,5	19	10	33	3,5	2,6	12	20	6	6	8
K0254.0310	stainless steel	black grey RAL 7021	M10	40	19	23	13	41	4	3	15	25	7	10	10
K0254.03101	stainless steel	orange RAL 2004	M10	40	19	23	13	41	4	3	15	25	7	10	10
K0254.03102	stainless steel	signal green RAL6032	M10	40	19	23	13	41	4	3	15	25	7	10	10
K0254.03103	stainless steel	blue RAL5017	M10	40	19	23	13	41	4	3	15	25	7	10	10
K0254.03105	stainless steel	light grey RAL 7035	M10	40	19	23	13	41	4	3	15	25	7	10	10
K0254.03106	stainless steel	traffic red RAL 3020	M10	40	19	23	13	41	4	3	15	25	7	10	10
K0254.03107	stainless steel	colza yellow RAL 1021	M10	40	19	23	13	41	4	3	15	25	7	10	10
K0254.0412	stainless steel	black grey RAL 7021	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
K0254.04121	stainless steel	orange RAL 2004	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
K0254.04122	stainless steel	signal green RAL6032	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
K0254.04123	stainless steel	blue RAL5017	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
K0254.04125	stainless steel	light grey RAL 7035	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
K0254.04126	stainless steel	traffic red RAL 3020	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13
K0254.04127	stainless steel	colza yellow RAL 1021	M12	50	24	31	16	51	5,5	4,5	20	30	8	8	13