


## Edge protection profiles with steel retaining strip

### Item description/product images



Minimum bend radius:



### Description

**Material:**  
PVC.

**Version:**  
Black.

**Note:**

The edge protection profiles are used to cover and decorate the sharp edges of cut plate so that no additional processing is required.


**Assembly:**

Easy, quick and smooth assembly. The edge protection profile is easy to push on by hand, and remains in place even on radii or bends. No adhesive or fastening material required.

**On request:**

Other lengths.

### Drawings



### Overview of items

#### Edge protection profiles with steel retaining strip

Order No.	Form	L	Clamping range mm	Minimum bend radius mm	B	H
K1367.010X2000	A	2000	1,0-2,0	A=15 B=15 C=10 D=10	6,5	10
K1367.010X5000	A	5000	1,0-2,0	A=15 B=15 C=10 D=10	6,5	10
K1367.010X10000	A	10000	1,0-2,0	A=15 B=15 C=10 D=10	6,5	10
K1367.010X20000	A	20000	1,0-2,0	A=15 B=15 C=10 D=10	6,5	10
K1367.010X50000	A	50000	1,0-2,0	A=15 B=15 C=10 D=10	6,5	10
K1367.114X2000	B	2000	1,0-4,0	A=30 B=20 C=20 D=20	10	14,5
K1367.114X5000	B	5000	1,0-4,0	A=30 B=20 C=20 D=20	10	14,5
K1367.114X10000	B	10000	1,0-4,0	A=30 B=20 C=20 D=20	10	14,5
K1367.114X20000	B	20000	1,0-4,0	A=30 B=20 C=20 D=20	10	14,5
K1367.114X50000	B	50000	1,0-4,0	A=30 B=20 C=20 D=20	10	14,5
K1367.217X2000	C	2000	4,0-6,0	A=50 B=40 C=30 D=30	11	15,8
K1367.217X5000	C	5000	4,0-6,0	A=50 B=40 C=30 D=30	11	15,8
K1367.217X10000	C	10000	4,0-6,0	A=50 B=40 C=30 D=30	11	15,8
K1367.217X20000	C	20000	4,0-6,0	A=50 B=40 C=30 D=30	11	15,8
K1367.217X50000	C	50000	4,0-6,0	A=50 B=40 C=30 D=30	11	15,8
K1367.308X2000	D	2000	0,8-1,5	A=10 B=10 C=10 D=10	6	8
K1367.308X5000	D	5000	0,8-1,5	A=10 B=10 C=10 D=10	6	8
K1367.308X10000	D	10000	0,8-1,5	A=10 B=10 C=10 D=10	6	8
K1367.308X20000	D	20000	0,8-1,5	A=10 B=10 C=10 D=10	6	8
K1367.308X50000	D	50000	0,8-1,5	A=10 B=10 C=10 D=10	6	8
K1367.415X2000	E	2000	6,0-8,0	A=50 B=50 C=50 D=50	12	15

## Edge protection profiles with steel retaining strip

### Overview of items

Order No.	Form	L	Clamping range mm	Minimum bend radius mm	B	H
K1367.415X5000	E	5000	6,0-8,0	A=50 B=50 C=50 D=50	12	15
K1367.415X10000	E	10000	6,0-8,0	A=50 B=50 C=50 D=50	12	15
K1367.415X20000	E	20000	6,0-8,0	A=50 B=50 C=50 D=50	12	15
K1367.415X50000	E	50000	6,0-8,0	A=50 B=50 C=50 D=50	12	15