

# Technical information for NC vices

## Adaptable

Slot and thread for attachment jaws and gripper inserts.

## Optional

### Multiple clamping

Several workpieces can be clamped using reversible jaws. Tools are not required for installation.

## Individual

Flexible – can be used for any machine table, ready to use immediately with clamp strap set and slot keys (optional).

## Optimum positioning

Cross slot for alignment.

## Quick pre-adjustment

Locking pins for quick pre-positioning.

## Spindle drive

Mechanical-hydraulic version up to 40 kN or purely mechanical clamping up to 10 kN.

## Impressive advantages:

- Repeat accuracy  $\leq 0.01$  mm
- Fixed jaw fixed in all directions (X,Y,Z)
- Wide clamping range due to use of attachment step jaws
- Basic equipment: 2 rotating screw-in jaws and 1 crank handle
- Can be inclined sideways, with fastening holes for slot spacing of 63 mm and 100 mm.

